

INSULATING RUBBER GLOVES AND ACCESSORIES

Your high voltage gloves must be tested, date stamped, and certified every 6 months. How can we help?

OSHA Certification Requirements

All Cementex gloves are ship tested and certified according to OSHA regulation 1910.137(b)(2)(xii) which states the employer shall certify that equipment has been tested in accordance with the requirements of paragraph (b)(2)(vii), (b)(2)(ix), and (b)(2)(xi) of this section. The certification shall identify the equipment that passed the test and the date it was tested.



Manufactured in ISO facilities: The insulating rubber gloves provided by Cementex Products Inc. are compliant with OSHA 1910.137, OSHA 1910.268, NFPA 70E, CSA Z462, and exceed the ASTM D120 and European EN60903 standards for use around Electrical Hazards and Arc Flash Protection.

Made of natural rubber; these gloves offer the required dielectric insulation combined with flexibility, strength, and durability. Chlorinated for maximum comfort; gloves feature rolled cuffs and anatomical shape reducing hand fatigue. Available in whole and half sizes: Black, Red or Yellow.



SIZING: Measure the circumference of the palm as shown. Round up to the nearest whole number = size.

Insulating Glove Kits

Insulating Glove Kit, IGK00-11-10R Includes Rubber/Leather/Canvas Storage Bag IGK(Class)-(Length)-(Size)(Color) 00-4 11-18* 8-12 R/B/Y

Insulating Gloves Only

Insulating Clove, IG2-14-10B, Stk# 278X311 IG(Class)-(Length)-(Size)(Color)

00-4 11-18* 8-12 R/B/Y

Leather Protectors

Leather Protector, P2-12-10 Designed to be worn over insulating rubber gloves for mechanical and arc flash protection P(Class)-(Length)-(Size)

Canvas Storage Bags

* see full catalog for available configurations

CGB(Size) 14-16-20

Glove Liners

Glove Liners, COTGLV, Stk# 278X166

Gemen(ex

ALWAYS

WEAR

YOUR

GLOVES

For added comfort, sizing adjustment, and moisture control COTGLV10" Cotton WOLGLV1010" Wool

Glove Inflator

<u>CPGI Glove Inflator, Stk# 278X175</u> Allows for complete physical inspection of rubber gloves CPGI......Glove Inflator

<u>Glove Talc</u>

CGT-6SB, 6oz. Bottle, Stk# 278X173

Designed for safe use with insulating rubber products. Will not damage type 1 or type 2 rubber CPGT-(Size/Type*)

Rubber Goods Cleaner

Will not damage sensitive rubber goods CPIGC......1 Gallon Liquid CPGW-72D6.......Rubber Goods Wipes

Specialized Products

www.specialized.net

Debbi Kosakowski - National Sales Manager ckosakowski@specialized.net • 727-515-0911 Eleanor Barszowski - NE Regional Sales Manager ebarszowski@specialized.net + 484-955-3178 Carolyn Thompson yn@specialized.net • 800-794-1500